

# ReoGrand™

**KING**®  
L I V I N G




DT2017478 V11


[kingliving.com](http://kingliving.com)

# ReoGrand Components


**720R (Recliner) LH Arm**  
**720F (Fixed) LH Arm**  
Front View




**720R (Recliner) LH Arm**  
Rear View




**720F (Fixed) LH Arm**  
Rear View




**720R (Recliner) LH Arm**  
**720F (Fixed) LH Arm**  
Headrest with 15 Levels




**720R (Recliner) LH Arm**  
Reclined




**720R (Recliner) SMART LH Arm**  
**720F (Fixed) SMART LH Arm**  
Headrest with 15 Levels




**720R (Recliner) SMART LH Arm**  
Reclined




**720R (Recliner) RH Arm**  
**720F (Fixed) RH Arm**  
Front View




**720R (Recliner) RH Arm**  
Rear View




**720F (Fixed) RH Arm**  
Rear View




**720R (Recliner) RH Arm**  
**720F (Fixed) RH Arm**  
Headrest with 15 Levels




**720R (Recliner) RH Arm**  
Reclined




**720R (Recliner) SMART RH Arm**  
**720F (Fixed) SMART RH Arm**  
Headrest with 15 Levels



**720R (Recliner) SMART RH Arm**  
Reclined



**720R (Recliner)**  
**720F (Fixed)**  
Front View




**720R (Recliner)**  
**Armless**  
Rear View




**720F (Fixed)**  
**Armless**  
Rear View




**720R (Recliner)**  
**720F (Fixed)**  
Headrest with 15 Levels




**720R (Recliner)**  
Reclined



**Corner 800**  
**800F (Fixed) Module**  
**800F (Fixed) Module SMART**



Top View



Effective December 2020, ReoGrand Recliners use TouchGlide® Technology. The weight limit for the recliner mechanism used in ReoGrand Recliner is 120kg (264.5lb). The weight limit for ReoGrand Recliner footrest is 15kg (33lb). As King Living has a policy of continuous improvement, changes to products and specifications may be made without prior notice. Images and drawings are representative of design only. Accessories not included.

**IMPORTANT: ALWAYS FULLY RETRACT THE FOOTREST BEFORE SITTING IN OR GETTING OUT OF THE RECLINER.** To avoid damage to your recliner, the reclining function should only be operated when you are seated in the recliner. Any open footrests, which have a 15kg (33lb) weight limit, must be closed before getting out of or into the seat. Sliding forward over the footrest to get out of the seat or getting into a fully reclined seat may cause damage to the mechanism of the recliner and can result in the sofa tipping forward in extreme cases. This built-in tipping point was specifically designed to preserve the integrity of the mechanism if too much pressure is placed on it and to avoid permanent damage. Damage caused by improper use of Recliners will not be covered under Warranty.

# ReoGrand Components


## 2STR 720RF RH Arm / 2STR 720RF RH Arm SMART

Front View  
Headrest Down  
Rear View




## 2STR 720RF RH Arm

Side View (Reclined)  
Headrest 15 Levels




## 2STR 720RF RH Arm SMART

Side View (Reclined)  
Headrest 15 Levels




## 2STR 720RF LH Arm / 2STR 720RF LH Arm SMART

Front View  
Headrest Down  
Rear View



## 2STR 720RF LH Arm

Side View (Reclined)  
Headrest 15 Levels




## 2STR 720RF LH Arm SMART

Side View (Reclined)  
Headrest 15 Levels




## Chaise 720F RH Arm / Chaise 720F RH Arm SMART

Front View  
Headrest Down  
Rear View




## Chaise 720F RH Arm

Side View  
Headrest 15 Levels



## Chaise 720F RH Arm SMART

Side View  
Headrest 15 Levels




## Chaise 720F LH Arm / Chaise 720F LH Arm SMART

Front View  
Headrest Down  
Rear View



## Chaise 720F LH Arm

Side View  
Headrest 15 Levels



## Chaise 720F LH Arm SMART

Side View  
Headrest 15 Levels




Effective December 2020, ReoGrand Recliners use TouchGlide® Technology. The weight limit for the recliner mechanism used in ReoGrand Recliner is 120kg (264.5lb). The weight limit for ReoGrand Recliner footrest is 15kg (33lb). As King Living has a policy of continuous improvement, changes to products and specifications may be made without prior notice. Images and drawings are representative of design only. Accessories not included.


**IMPORTANT: ALWAYS FULLY RETRACT THE FOOTREST BEFORE SITTING IN OR GETTING OUT OF THE RECLINER.** To avoid damage to your recliner, the reclining function should only be operated when you are seated in the recliner. Any open footrests, which have a 15kg (33lb) weight limit, must be closed before getting out of or into the seat. Sliding forward over the footrest to get out of the seat or getting into a fully reclined seat may cause damage to the mechanism of the recliner and can result in the sofa tipping forward in extreme cases. This built-in tipping point was specifically designed to preserve the integrity of the mechanism if too much pressure is placed on it and to avoid permanent damage. Damage caused by improper use of Recliners will not be covered under Warranty.

# ReoGrand Sofa Bed


Side View  
Headrest Down




Side View  
(SMART Pockets™)  
Headrest 15 Levels




Front View  
Headrest Up




Back View  
Headrest Down



Bed Position  
Side View – Unfolded




Bed Position  
Top View – Unfolded




# SMART Pocket™ Accessories


PocketAccessory  
Table CRES  
Side View / Top View



PocketAccessory  
Charge Table CRES  
Side View / Top View



PocketAccessory  
SMART Speaker Bracket Pair  
Sonos Play 1  
Side View / Top View



PocketAccessory  
SofaLight 1214  
Side View



Effective December 2020, ReoGrand Recliners use TouchGlide® Technology. The weight limit for the recliner mechanism used in ReoGrand Recliner is 120kg (264.5lb). The weight limit for ReoGrand Recliner footrest is 15kg (33lb). Table Tops, and Sofa Lights available in selected King Living Timber Finishes. As King Living has a policy of continuous improvement, changes to products and specifications may be made without prior notice. Images and drawings are representative of design only. Accessories not included.

**IMPORTANT: ALWAYS FULLY RETRACT THE FOOTREST BEFORE SITTING IN OR GETTING OUT OF THE RECLINER.** To avoid damage to your recliner, the reclining function should only be operated when you are seated in the recliner. Any open footrests, which have a 15kg (33lb) weight limit, must be closed before getting out of or into the seat. Sliding forward over the footrest to get out of the seat or getting into a fully reclined seat may cause damage to the mechanism of the recliner and can result in the sofa tipping forward in extreme cases. This built-in tipping point was specifically designed to preserve the integrity of the mechanism if too much pressure is placed on it and to avoid permanent damage. Damage caused by improper use of Recliners will not be covered under Warranty.

# ReoGrand™ Packages

**KING**®  
L I V I N G



DT201 8680 V4


[kingliving.com](http://kingliving.com)

# ReoGrand™ Packages

## RH Chaise Corner Package 4

Additional Package\* **SMART**


1x 2STR 720RF Module LH Arm, 1x Corner 800 FIXED Module,  
2x Chair 720 FIXED Module, 1x Chaise 720F Module RH Arm



## LH Chaise Corner Package 4

Additional Package\* **SMART**


1x 2STR 720RF Module RH Arm, 1x Corner 800 FIXED Module,  
2x Chair 720 FIXED Module, 1x Chaise 720F Module LH Arm



## Corner Package 2

Additional Package\* **SMART**


2x Chair 720F Module, 1x Chair 720R Module LH Arm,  
1x Chair 720R Module RH Arm, 1x Corner 800F Module



## RH Chaise Pkg 3 RFC

Additional Package\* **SMART**


1x Chaise 720F Module RH Arm,  
1x 2STR 720RF Module LH Arm



## LH Chaise Pkg 3 CFR

Additional Package\* **SMART**


1x Chaise 720F Module LH Arm,  
1x 2STR 720RF Module RH Arm



## 3 Seater RFR

Additional Package\* **SMART**


1x Chair 720R Module LH Arm,  
1x Chair 720R Module RH Arm,  
1x Chair 720F Module



## Sofa Bed 1600-2070W

Additional Package\* **SMART**

1x ReoGrand Sofa Bed Frame 1600/2070W,  
1x Sofa Bed Mattress 1600



Effective January 2019, ReoGrand Recliners use TouchGlide® Technology. The weight limit for the recliner mechanism used in ReoGrand Recliner is 120kg (264.5lb). The weight limit for ReoGrand Recliner footrest is 15kg (33lb).

\*Additional Package: SMART: SMART Arms replace STD Arms. As King Living has a policy of continuous improvement, changes to products and specifications may be made without prior notice. Images and drawings are representative of design only. Accessories not included.

**IMPORTANT: ALWAYS FULLY RETRACT THE FOOTREST BEFORE SITTING IN OR GETTING OUT OF THE RECLINER.** To avoid damage to your recliner, the reclining function should only be operated when you are seated in the recliner. Any open footrests, which have a 15kg (33lb) weight limit, must be closed before getting out of or into the seat. Sliding forward over the footrest to get out of the seat or getting into a fully reclined seat may cause damage to the mechanism of the recliner and can result in the sofa tipping forward in extreme cases. This built-in tipping point was specifically designed to preserve the integrity of the mechanism if too much pressure is placed on it and to avoid permanent damage. Damage caused by improper use of Recliners will not be covered under Warranty.